

Весовой индикатор BSA-207

Инструкция по эксплуатации



Ver.2015

1.	-----	3
2.	-----	3
3.	-----	4
4.	-----	5
5.	-----	5
5.1	-----	5
5.2	-----	6
5.3	-----	7
6.	USB -----	7

1.

1.1 - 0 V ~ 16 mV

1.2 - 0.15 $\mu\text{V}/^\circ\text{C}$

1.3 - 12 ppm/ $^\circ\text{C}$

1.4 - 5 ~ 20 HZ

1.5 - III

1.6 - 0.01% F.S

1.7 - 4 (8V, 350)

1.8 - 0 ~ 40 $^\circ\text{C}$

1.9 - -25 ~ 55 $^\circ\text{C}$

1.10 () - 90%RH

1.11 - 1 / 2 / 5

1.12 - 6 , 0.8 , 7- LED

1.13 - 600, 1200, 2400, 4800 9600

1.14 - AC220V(+10%~ -15%) 50Hz \pm 1HZ

1.15 (x x) - 20 \times 15 \times 4.5 ()

1.16 - 2 .

2.

2.1 - 20 000

2.2

2.3


2.4

2.5

2.6

2.7 USB-

3.



:



5.2

FUNC,
FUNC
FUNC

FUNC

5.2.1

FUNC

<L.

.xxx>, «L» - , « . » -

ZERO,

<dEnSit>

2-

<1.000> (

).

SUM

kg/lb,

ZERO

FUNC

<L. .xxx>.

5.2.2

FUNC

<P.150>,

« » - , <x.xxx> -

ZERO,

<PIECE>

<1.000> (

).

SUM kg/lb

ZERO

FUNC

<P.xxx>

